

# Cleanpartiner 255

Super polished mirror enclosure the most sophisticated on the market

### Decontamination extraction station

# DSS6 series


DSS6 is the largest extraction station for Cleanpart'ner particle trackers. It allows to extract the contamination in order to evaluate the level of cleanliness of the parts according to the cleanliness standard which are, among others, the ISO 16232 and the VDA19

### Benefits

- Ovoid extraction enclosure to minimize particle retention, super polished mirror finish, Ra 0.02
- Fast and repeatable blank acquisition, value less than 250  $\mu m$ , 200  $\mu m$  as a minimum
- Automatic Wall flushing integrated into walls without risk of particles retention
- Full access to the extraction area (optional sliding window)
- Double air supply flow and exhaust air extraction, integrated into the station (operator protection)
- Laminar air flow with HEPA filter 0,3 μm meet a class 5 max. according to ISO 14644
- Touch colour machine interface with functional and intuitive controls
- Designed and manufactured in our workshops
- Quality of finishes and choice of materials to avoid particle generation and retention
- HMI located on the right side to allow the installation of a manipulator arm for very heavy components (max. 500 Kg)
- Proven and reliable equipment




| Dimensions   | Width (mm)      | Depth (mm) | Height (mm) |
|--------------|-----------------|------------|-------------|
| Working area | 2067/ 1883 max. | 1490       | 1340        |
| Overall      | 2750            | 1880       | 3350        |









## **Technical informations**

EC fully compliant - Comply with the European Machinery Directives 2006 and Electromagnetic compatibility

Two types of PLC available as standard: SIEMENS

Pen flow rate: adjustable 10 L/mn max. - Walls flushing: 30 L/mn max.

Rinsing pressure: 4,5 bar max.

Useful volume tank: 100 litres

Membrane holder: Ø 47 or 90 mm - Optional cascade of 3 membranes

Fluid filtration rate: 1 / 0,2 µm

Accepted types of fluid: solvent or detergent (water base)

Materials: 304L stainless-steel polished bowl - Painted steel for

structure

Fine textured powder paint

Extraction connection: 304 mm outside

### Accessories








Cascade membrane holder Ø47 or 90 mm



Stainless-steel bowl with integrated membrane holder for small parts



HDPE support plate

# Choose your configuration

|      | НМІ             | Finishes                                     | Window      | Power supply               |
|------|-----------------|----------------------------------------------|-------------|----------------------------|
| DSS6 | □ S SIEMENS 15" | ☐ 2P Painted frame ☐ 2S Full stainless-steel | R Removable | □ C 440 V – 3 phases 60 Hz |



Cleanpart'ner and its particle trackers specifically meet your needs and the geometry of your parts which require an adapted response.